



Powering Business Worldwide

pe.eaton.com

1 in Type BR EUSERC Residential Meter Breaker

MBE1224B125BTS

UPC:782114890813

Dimensions:

- **Height:** 23.88 IN
- **Length:** 5.38 IN
- **Width:** 14.44 IN

Weight:40 LB

Warranties:

- 10 year

Specifications:

- **Type:** All-in-ones
- **Amperage Rating:** 125A
- **Box Size:** A
- **Bus Material:** Aluminum
- **Enclosure:** NEMA 3R
- **Feed Type:** Overhead/underground
- **Ground:** #14-2/0 AWG
- **Interrupt Rating:** 10 kAIC
- **Line:** #6-250 kcmil
- **Main Circuit Breaker:** BR2125
- **Mounting:** Surface mounting
- **Number Of Circuits:** 24
- **Number Of Jaws:** Four-jaws
- **Number Of Sockets:** 1
- **Number Of Spaces:** 12
- **Phase:** Single-phase
- **Security:** Ring
- **Used With:** Type BR breakers
- **Voltage Rating:** 120/240V

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)



- [Technical Data Residential Meter Breakers:
Type CH and BR Residential](#)

Certifications:

- UL Listed

Product compliance:

- EUSERC Approved

© 2016 Eaton. All rights reserved.