



*Powering Business Worldwide*

[pe.eaton.com](http://pe.eaton.com)

## 1 in Type BR Solar Power Center Meter Breaker

**MBE1224PV125BTS**

**UPC:**786685690216

### **Dimensions:**

- **Height:** 23.9 IN
- **Length:** 5.31 IN
- **Width:** 14.45 IN

**Weight:**30 LB

### **Warranties:**

- 10 year

### **Specifications:**

- **Special Features:** Side by side construction
- **Type:** BR solar-ready
- **Amperage Rating:** 125A
- **Bus Material:** Aluminum
- **Bus Rating:** 125 A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Galvanized steel
- **Feed Type:** Overhead/underground
- **Input:** 25 max PV input
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** BR
- **Mounting:** Surface mounting
- **Number Of Circuits:** 24
- **Number Of Sockets:** 1
- **Number Of Spaces:** 12
- **Phase:** Single-phase
- **Used With:** Type BR breakers
- **Voltage Rating:** 120/240V
- **Box Size:** 2

### **Supporting documents:**

- [Solar power centers](#)
- [Eatons Volume 15-Solar Inverters and Electrical](#)



Balance of System

- [Eaton Specification Sheet - MBE1224PV125BTS](#)

**Certifications:**

- UL Listed

**Product compliance:**

- EUSERC Approved