



Actual

Catalog Number: CULL4-14TP
Product ID: 7TBA014470R0005
UPC Number: 78378667715
Status: Active

Copper Lay-In Lug, Wire Range #14 - #4 AWG, Stud Size 0.22 Inch, Height 0.78 Inch, Width 0.38 Inch, Length 1.07 Inches, Tin Plated

- Ideal for swimming pool grounding applications. Carries "DB" marking for direct burial.
- Open-faced design enables installer to quickly lay-in grounding conductor as jumper to multiple conduits with no break in ground conductor.

North American Specifications (UNSPSC)

UNSPSC	39121613 Grounding devices or assemblies
IGCC	4909 Grounding devices or assemblies
Brand Name	Blackburn
Type	Mechanical Grounding
Special Features	Ideal for swimming pool grounding applications. Carries "DB" marking for direct burial.
Standard	UL E9809
Conductor Material	Copper
Insulation	No

Packaging

Inner Quantity	25
Inner Dimensions (inches)	1x1x1
Outer Quantity	100
Outer Dimensions (inches)	8x6.75x4
Weight Uom	6.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com