


Grounding - Zinc

Images



[Download Photo Image](#)

[Download Dimensional Image](#)

Dimension A in Inches: 2.74
Dimension B in Inches: 4.00
Dimension C in Inches: 0.73
Dimension D in Inches: 3.37
Dimension E in Inches: 4.50

Application

Used in situations where wires have already been pulled through Rigid/IMC conduit, and an insulated Grounding bushing is required. Rated 150 Degree C. cULus listed. Patented

Product Information

Material: Zinc Alloy
Finish: Ball Burnished, Mirror Smooth,
Grounding Lug: Tin Electro-plate

Certifications & Codes:

Federal Specification Number: A-A-50553
NEMA Standard: FB-1
UL File Number: E20412
UL Standard: UL-514B
UNSPSC: 39121312
Patent Number: 7,182,611; 6,840,782;
8,419,449

Catalog ID: SGB-389CL

UPC Number: 78174790389

Description: Split Bushing, Insulated, Grounding, Zinc Die Cast, Size 3-1/2 Inch, 14-1/0 Lug

Application: Used in situations where wires have already been pulled through Rigid/IMC conduit, and an insulated Grounding bushing is required. Rated 150 Degree C. cULus listed. Patented

Trade Size: 3-1/2"

Std Pkg Qty: 25

Unit Qty: -