PatchLink™ Horizontal Cable Managers



specifications

Horizontal cable managers shall be capable of managing cables on the front and rear of any 19" EIA rack. The manager shall consist of a 1-piece construction that is molded out of plastic. Horizontal managers shall have pass through holes that incorporate integral bend radius control as well as fingers with rounded edges. The manager shall have rigid end fingers that incorporate integral bend radius control. Hinged covers shall allow access to the cable pathway without having to completely remove the cover from the manager.



technical information

Dimensions:

Part Number	RU	Height in (mm)	Width in (mm)	Depth in (mm)	
WMP1E	2	3.5 (88.9)	19.0 (482.6)	8.9 (225.5)	
WMPF1E	2	3.5 (88.9)	19.0 (482.6)	3.7 (93.7)	
WMPH2E	2	3.5 (88.9)	19.0 (482.6)	8.9 (225.5)	
WMPHF2E	2	3.5 (88.9)	19.0 (482.6)	3.7 (93.7)	
WMPSE	1	1.7 (44.1)	19.0 (482.6)	8.9 (225.5)	
WMPFSE	1	1.7 (44.1)	19.0 (482.6)	3.7 (93.7)	
WMPLSE	1	1.7 (44.1)	19.0 (482.6)	7.9 (200.1)	
WMPLFSE	1	1.7 (44.1)	19.0 (482.6)	2.7 (69.1)	

Packaging:

Cable managers include hinged cover(s), mounting hardware

key features and benefits

Integral bend radius control

Maintains bend radii as cables transition to and from horizontal and vertical pathways

Dual hinged coverOpens upward or downward to provide easy access to cables in horizontal pathway without having to completely

remove cover

Increased finger spacing Provides larger area for high performance Category 6 cables

One piece, plastic construction Provides durability and easy installation

Flexible fingers Provide for easy installation and organizes cables simplifying

moves, adds, and changes

Rounded edges on fingersProtect cables from snags and damage to cableCable pass through holesProvide ease of installation and cable maintenance

applications

Panduit® PatchLink™ Horizontal Cable Managers provide a neat and efficient way to manage patch cables on any EIA 19" rack. They can be used in multimedia applications to manage copper, fiber optic, and coax cables. Flexible fingers organize the patch cords simplifying moves, adds, and changes while the integral bend radius control and "closed" design protects the patch cables in the pathway. All of these features combine to provide the user with a horizontal

cable management solution that simplifies cable routing in a finished, professional appearance. When used with the Panduit® Mini-Com® patch panels, patch cords, vertical cable managers, and racks, the user receives a total system that satisfies functional and aesthetic requirements for telecommunications rooms.

2 RU Managers

Front and Rear, with

bend radius clips: WMPH2E Front and Rear: WMP1E

Front Only, with

bend radius clips: WMPHF2E

Front Only: WMPF1E

1 RU Managers

Front and Rear: WMPSE

Front and Rear,

short depth: WMPLSE Front Only: WMPFSE

Front Only,

short depth: WMPLFSE

Racks

2 post 19"

EIA standard rack: R2P^ 4 post rack 7' 30" depth with #12-24 threaded rails: R4P*^

4 post rack 7' 23" depth with #12-24 threaded rails: R4P23*^

4 post rack 7' 36" depth with #12-24 threaded rails: R4P36*^

4 post rack 7' 42" depth with #12-24 threaded rails: R4P42*^

Panel Extender Brackets

1 RU: PEB1 **2 RU:** PEB2

Accessories


Cable retainers: WR3E-X

*Add "CN" for Cage Nut Rails

^Add suffix 96 to the end of the part number for 8 foot versions.

www.panduit.com

PatchLink™ Horizontal Cable Managers



All managers have 17" long front covers except for the WMPH2E and WMPHF2E, which have19 3/8" long front covers for complete coverage to vertical managers.

Cable Capacity Chart


Part Number	Front				Rear					
	Channel Area (in²)	Cat. 6A (28AWG - 0.185")	Cat. 6A (24AWG - 0.275")	Cat. 6 (28AWG - 0.150")	Cat. 6 (24AWG - 0.235")	Channel Area (in²)	Cat. 6A (28AWG - 0.185")	Cat. 6A (24AWG - 0.275")	Cat. 6 (28AWG - 0.150")	Cat. 6 (24AWG - 0.235")
WMP1E WMPF1E	6.8	101	45	153	62	9.1 -	134 -	60 -	204 -	83 -
WMPH2E WMPHF2E	6.8	101	45	153	62	9.1 -	134 -	60 -	204 -	83 -
WMPSE WMPFSE	2.7	40	18	61	25	4.6 -	68 -	30 -	104 -	42 -
WMPLSE WMPLFSE	1.7	25	11	38	15	4.6 -	68 -	30 -	104 -	42 -

Dimensions are in inches. (Dimensions in parenthesis are metric.)

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA Markham, Ontario cs-cdn@panduit.com Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK cs-emea@panduit.com Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan cs-japan@panduit.com Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Jalisco, Mexico cs-la@panduit.com Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



Contact Customer Service by email: cs@panduit.com or by phone: 800-777-3300 © 2016 Panduit Corp. ALL RIGHTS RESERVED. **RKSP154--WW-ENG** Replaces WW-RKSP46 5/2016

