

4U Series 12V Xenon Collection

8" Xenon Harmonization 12V Cabinet Light - BZT

4U12X08BZT (Bronze Textured)



Dimensions

Height	1.25"
Length	8.00"
Width	4.50"

Project Name: _____

Location: _____

Type: _____

Qty: _____

Comments: _____

Ordering Information

Product ID	4U12X08BZT
Finish	Bronze Textured
Available Finishes	WHT, BZT, NIT
Collection	4U Series 12V Xenon Collection

Dimensions

Weight	1.00 LBS
--------	----------

Specifications

Material	Aluminum
Diffuser Description	Frosted

Electrical

Dimmable	Yes
Voltage	108-132V
Input Voltage	Single(120)
Operating Voltage Range	108-132V
Switch Type	Hi-Low-Off, Rocker

Qualifications

Safety Rated	Dry
Expected Life Span	10000 Hours
Warranty	www.kichler.com/warranty

Installation

Wire Connectors	Wire Nuts
Direct Wire	Yes
Knockouts	0.5 in
Number of Knockouts	4
Modular	Yes

Primary Lamping

Light Source	Incandescent
Lamp Included	Included
# of Bulbs/LED Modules	1
Max or Nominal Watt	18W
Socket Type	Wedge T5
Bulb Product ID	10574CLR
Dimming	Yes