



GE
Lighting

35523 - GE LED Bright Stik™

LED16LS2/828

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Primary Application	General Purpose
Product Color	White
Product Technology	LED
Rated Life (Hours)	15000 h
Lamp Count	2
Life in Years	13.7 yr
Replacement Watts	100 W
Requested Structure	Carton
Estimated Energy Cost per Year	1.93
Base	E26
Bulb Shape	A21

PHOTOMETRIC CHARACTERISTICS

Lumens per Watt (Efficacy)	95 lm
Nominal Initial Lumen per Watt	95
Initial Lumens-nominal	1520 lm
Color Rendering Index-CRI	88
Color Temperature	2850 K

PRODUCT INFORMATION

Product Code	35523
Description	LED16LS2/828
Alternative Unit Of Measure	EACH
Standard Package Quantity	16
Ean UPC	043168355230
Standard Package GTIN	00043168355230
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	16
Sales Unit	Each
UCC	043168355230
Alternative Unit Of Measure	CASE
Standard Package Quantity	16
Ean UPC	043168355230
Standard Package GTIN	10043168355237
No Of Items Per Sales Unit	
No Of Items Per Standard Package	16
Sales Unit	Case
UCC	043168355230

DIMENSIONS

Bulb Max Overall Length-MOL	5.31 mm
-----------------------------	---------

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Input Voltage [nom]	120 V
Rated power (Watts)	16 W