

Item #: 12427-0	UPC Code: 747396802060
Product Family Name:	Finish: Polished Nickel with Mercury Glass
Category: Table Lamp	Category Type: Table Lamp
Certification E341302	
Patents	
Notes:	



Image File Name:
12427-0--
1422439810.jpg



MEASUREMENTS

Width: 11	Length: 18	Height: 29	Extension:
Height Adjustable: No	Min Overall Height:	Max Overall Height:	Slope: No
Wire Length: 96	Chain Length:	Safety Cable Included: No	Net Weight: 9.48
Canopy Width:	Canopy Height:	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs: 1	Light Type: A-19,Med			
Max Bulb Wattage: 100	Socket: E26,Medium			
Dimmable: No	Ballast:	Rated Life Hours:	Photocell Included: N	Lamps Included: No
Lamp Included: No	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description:	Material: Fabric
Part No.: RS12427	Quantity: 1
Width: 18	Height: 11
	Length: 11



SHIPPING

Carton Width: 19	Carton Height: 12.25	Carton Length: 24
Carton Weight: 12.98	Carton Cubic Feet: 3.233	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		Master Pack: 1



UL Listed

Yes