

|  |                                     |
|--|-------------------------------------|
| Item #:<br><b>10821-0</b>  | UPC Code:<br>840253039460           |
| Product Family Name:   | Finish:<br><b>LACONIA</b>           |
| Category:<br><b>Table Lamp</b>                                   | Category Type:<br><b>Table Lamp</b> |
| Certification<br><b>E250256</b>                                  |                                     |
| Patents  |                                     |
| Notes:<br><b>California Title 20 Compliant CFL Bulb Included</b> |                                     |



Image File Name:  
10821-0--  
1509036029.jpg



## MEASUREMENTS

|                                 |                      |                                     |                            |
|---------------------------------|----------------------|-------------------------------------|----------------------------|
| Width:<br><b>10</b>             | Length:<br><b>14</b> | Height:<br><b>28</b>                | Extension:                 |
| Height Adjustable:<br><b>No</b> | Min Overall Height:  | Max Overall Height:                 | Slope:<br><b>No</b>        |
| Wire Length:<br><b>96</b>       | Chain Length:        | Safety Cable Included:<br><b>No</b> | Net Weight:<br><b>7.61</b> |
| Canopy Width:                   | Canopy Height:       | Canopy Length:                      |                            |
| Backplate Width:                | Backplate Height:    | Center to Top:                      | Center to Bottom:          |

## LAMPING

|                                 |                                |                   |                     |                              |
|---------------------------------|--------------------------------|-------------------|---------------------|------------------------------|
| No. of Bulbs:<br><b>1</b>       | Light Type:<br><b>A21, Med</b> |                   |                     |                              |
| Max Bulb Wattage:<br><b>100</b> | Socket:<br><b>E26, Medium</b>  |                   |                     |                              |
| Dimmable:<br><b>No</b>          | Ballast:                       | Rated Life Hours: | Photocell Included: | Lamps Included:<br><b>No</b> |
| Lamp Included:<br><b>No</b>     | Color Temp.:                   | CRI:              | Initial Lumens:     | Delivered Lumens:            |

## SHADE / GLASS

|                               |                            |                         |
|-------------------------------|----------------------------|-------------------------|
| Description:                  | Material:<br><b>Fabric</b> |                         |
| Part No.:<br><b>RSG0611-4</b> | Quantity:                  |                         |
| Width:<br><b>10.00</b>        | Height:<br><b>10.50</b>    | Length:<br><b>14.00</b> |



## SHIPPING

|                                |                                    |  |                          |
|--------------------------------|------------------------------------|--|--------------------------|
| Carton Width:<br><b>11.500</b> | Carton Height:<br><b>24.000</b>    | Carton Length:<br><b>15.000</b>        |                          |
| Carton Weight:<br><b>9.284</b> | Carton Cubic Feet:<br><b>2.396</b> | Small Package Shippable:<br><b>Yes</b> |                          |
| Master Pack Width:             | Master Pack Height:                | Master Pack Length:                    |                          |
| Master Pack Weight:            | Master Cubic Feet:                 | Multi-Pack:<br><b>1</b>                | Master Pack:<br><b>1</b> |



Title 17

Yes



Title 20

Yes



UL Listed

Yes