



DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



Linear fluorescent

P7128-30EB

Linear Fluorescent Bath

Utility bath bracket with extruded ribbed white acrylic diffuser and white end caps. Knockout for G.C.O. and switch. Mount horizontally or vertically. Standard 120V HPF electric ballast.

Width: 24-3/8"

Height: 4-5/8"

Depth: 4"

Category: Bath & Vanity

Finish: White

Construction: Steel construction

Glass: White acrylic diffuser

Length: 23-3/8" L

Height: 4-5/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall horizontal or vertical mounted Mounts in "up" or "down" position Chassis covers a standard 4" hexagonal recessed outlet box	Pre-wired 6" of wire supplied 120V HPF electronic 120V	Quantity: 1 17W F17T8 Bi-pin twist-in base lamp holders	UL-CUL Damp location listed 1 year warranty Companion fixtures are available