



S9283

3MR11/LED/25'/5000K/12V
3 watt; LED; MR11; 5000K; 25' beam spread; 25000 Average
rated Hours; 210 Lumens; GU4 base; 12 volts

Features

- Solid State LED Lighting
- High Efficiency
- Long Life
- UL approved for totally enclosed fixtures
- 20watt halogen MR11 equivalency

View [Transformer Compatibility](#)



S9283

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9283	045923092831	12	3	20W	0.61	MR11	GU4
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
GU4	3MR11/LED/25'/5000K/12V	Non-Dimmable	White	1-3/8"	1-3/8"	210	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	CEC Status	RoHS Compliant	UL or ETL Listed	Warranty
5000	Natural Light	80	25	Lawful for sale in California	Yes	Yes	3 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

