

Marana Collection
Marana 2 Light Bath Light in Chrome CH
45612CH (Chrome)

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____

Ordering Information

Product ID	45612CH
Finish	Chrome
Available Finishes	CH, ORZ
Collection	Marana Collection

Dimensions

Extension	8.00"
Height from center of Wall opening	6.50"
Base Backplate	7.00 X 4.50 OVAL
Weight	3.17 LBS

Specifications

Material	Steel
Glass Description	Satin Etched Cased Opal

Electrical

Voltage	120V
---------	------

Qualifications

Safety Rated	Damp
Warranty	www.kichler.com/warranty

Installation

Install Glass Up or Down	Yes
--------------------------	-----

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
Number of Lights/LEDs	2
Max or Nominal Watt	100W
Socket Wire	150
Socket Type	Medium
Lamp Type	A19



Dimensions

Height	8.50"
Width	16.00"

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Hybrid	CFL	23-30W		