



CT SHORT BARREL SLEEVE



- Manufactured from high strength seamless copper tubing and Electro-Tin plated.
- Center Wire Stop.
- Chamfered barrel.
- Color Coded.
- Insures maximum cable insertion.
- UL 486A/B 90° C Listed and CSA Certified.
- 500 kcmil - 8 AWG, #8 - # 2 SOL UL467 Listed for grounding and bonding applications.
- Meets NEBS Level 3 requirements.
- If proper high voltage spacings and insulation techniques are used, may be used for high voltage applications up to 35KV.
- Expanded wire size with ILSCO dieless tools and Burndy Y644M dieless tool.
- For Copper Conductor only.
- Strand configurations:
- Copper - Class B concentric, Class B compressed, Class C concentric.
- Listed with IIsco tools ILC-12, ILC-12H, ILCB-12, ILC-14, ILC-14H, ILC-15, MT-25, 94285, IDT-12, IDT-12H, ILC-10, IDTB-12.
- IIsco connectors are UL Listed and CSA Certified with ILSCO or other Manufacturers' tools. Refer to Tool and Die Charts under Reference Tab.
- UL File E6207

Item ID	Conductor Size	Alternate Conductor Size	Expanded Conductor	Color Code	Die Index Number	Die Catalog Number	Length	Outside Diameter	Inside Diameter	Standard Package	NAED/UPC Number
CT-750	750 kcmil	600 G,H,I,M FLEX 646.4	750 kcmil - 500 kcmil	BLACK	I-106	ILD-106	3.3750	1.3130	1.0310	3	0783669126303