



Item #: **F696-CC**
 Product Family Name: **Kafé-XL**
 Category: **Interior Fan**
 Certification: **4000048**
 Patents
 Notes:

UPC Code: **706411042768**
 Finish: **Cognac**
 Category Type: **Ceiling Fan**



Image File Name:
 F696-CC--
 1509648332.jpg



MEASUREMENTS

Blade Finish:		Reversible Blades:	
		No	
Blade Material:		Slope:	
Plywood Construction		Yes	
Blade Sweep:	No. of Blades:	Blade Pitch:	Hanging Weight:
60	5	12	22.62
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:
6	0.75		
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:
15.00	12.75	80	188 X 20mm

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	42				153
Amps:	0.24				0.71
Watts:	9.940				84.460
CFM:	1497.00				6417.00
CFM/Watts:	150.60				75.98



FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
No	Yes	Yes
	Included Remote Control:	Included Wall Control:
	RCS212	
	Compatible Remote Control[s]:	Compatible Wall Control[s]:
		WCS212

LAMPING

No. of Bulbs:	Light Type:			
	N/A			
Max Bulb Wattage:	Socket:			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight
No	No			
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				

GLASS

Description:	Material:
Part No.:	Quantity:
Width:	Height:
	Length:



SHIPPING

Carton Width:	Carton Height:	Carton Length:
15.630	11.380	24.880
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
26.510	2.561	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		Master Pack:
		1



ENERGY
STAR
Yes



Title 17
Yes



ETL Intertek
Yes