

# QO325

## QO Mini CB 25 A 3P 120/240 V 10 kA Plug-in Mount

Product availability : Stock - Normally stocked in distribution facility



Price\* : 248.00 USD



### Main

|                             |                                                 |
|-----------------------------|-------------------------------------------------|
| Product or component type   | Miniature circuit-breaker                       |
| Range of product            | QO                                              |
| Line Rated Current          | 25 A                                            |
| System Voltage              | 120 V AC<br>120/240 V AC<br>240 V AC<br>48 V DC |
| Mounting mode               | Plug-in                                         |
| Poles description           | 3P                                              |
| Circuit breaker type        | Standard                                        |
| Circuit breaker application | HACR rated                                      |
| Electrical connection       | Pressure plate                                  |

### Complementary

|                           |                                                                                        |
|---------------------------|----------------------------------------------------------------------------------------|
| Breaking capacity         | 10 kA at: 120/240 V AC<br>5 kA at: 48 V DC<br>10 kA at: 120 V AC<br>10 kA at: 240 V AC |
| Number of spaces required | 3                                                                                      |
| AWG gauge                 | AWG 14...AWG 8 (copper or aluminium)                                                   |
| Height                    | 3 in                                                                                   |
| Depth                     | 2.91 in                                                                                |
| Width                     | 2.25 in                                                                                |

### Environment

|                        |                  |
|------------------------|------------------|
| Product certifications | CSA<br>UL listed |
|------------------------|------------------|

|                                       |                |
|---------------------------------------|----------------|
| Ambient air temperature for operation | 104 °F (40 °C) |
|---------------------------------------|----------------|

## Ordering and shipping details

|                       |                                   |
|-----------------------|-----------------------------------|
| Category              | 00012 - QO 3 POLE CIRCUIT BREAKER |
| Discount Schedule     | DE2A                              |
| GTIN                  | 00785901012467                    |
| Nbr. of units in pkg. | 3                                 |
| Package weight(Lbs)   | 0.8100000000000005                |
| Returnability         | Y                                 |
| Country of origin     | MX                                |

## Offer Sustainability

|                                  |                                                                                                                                                                                                                         |
|----------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status         | Green Premium product                                                                                                                                                                                                   |
| RoHS (date code: YYWW)           | Compliant - since 1323 - Schneider Electric declaration of conformity<br><a href="#"> Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                                                                                                  |
| Product environmental profile    | Available                                                                                                                                                                                                               |
| Product end of life instructions | Need no specific recycling operations                                                                                                                                                                                   |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|