

FM502ORB: 2 - Light Indoor Flush Mount

Dimensions:

Diameter:	13"	Wire:	8" (color/Brown)
Height:	6 1/2"	Mounting Proc.:	Universal Mounting Plate
		Connection:	Mounted To Box

Bulbs:

2 - Medium A19 60w Max. 120v - Not included

Features:

•

Material List:

1 Body - Steel - Oil Rubbed Bronze

Safety Listing:

Safety Listed for Damp Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (FM502)



Collection: Marteau

UPC #: 014817561609

Finish: Oil Rubbed Bronze (ORB)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Shantung	White Shantung	1	GLB044			5 1/2	12 1/2				
Diffuser	Glass	Sandblasted Outside / Silk Print Inside	1					13				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	3/4			10 5/8		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
--------------	-----------	----------	-----	--------	-------	--------	------	--------	-----------	----------

Individual	FM502ORB	1	014817561609	16.5	16	11.75	1.795	7.1	150	Yes
NJ Pallet		40		48	40	69.5	77.222	284		No
NV Pallet		40		48	40	69.5	77.222	284		No