
Typical Performance Technical Data Sheet


FEDERAL PACIFIC

Catalog No.T24SH2Y-75

-Characteristics	
Characteristics	
Phase	3
KVA	75
Primary	240∆
Secondary	208Y/120
Conductor	Aluminum
Temp. Rise	150° C
Frequency	60 HZ
Taps	+2, -4 x 2.5%
ESS	Yes
Insulation	220° C
Weathershield	WS-18
Wall Bracket	WMB-4
Weight (lbs)	685
Sound (dB)	50



AMP Ratings		



Notes


All units are UL listed and are designed in accordance with applicable NEMA, ANSI and IEEE standards.

Transformers are dry-type AA, ventilated NEMA 2 enclosure.

If a weathershield is indicated above this transformer can be converted to a NEMA 3R enclosure.

Transformers are floor mounted. Wall mounting bracket kit if shown above is optional and is supplied as a seperate accessory.

Paint color is ANSI 61.



Outline No: 08A3224