



8765-15: One Light Outdoor Wall Lantern



Collection: Polycarbonate Outdoor

Single Light Outdoor Fixture with White Finish and Clear Beveled Acrylic Panels

White polycarbonate outdoor wall lantern installs with or without tail. Clear beveled Acrylic panels. Virtually indestructible.

UPC #:785652876554

Finish: White (15)

Dimensions:

Width:	8"	Height wo/ Tail:	20"
Height:	25"	Extends:	9"
		Wire:	6 1/2"
		Mounting Proc.:	Cap Nuts
		Connection:	Mounted To Box
		Bulb Appearance:	Clear

Bulbs:

- 1 - Medium A19 100w Max. 120v - Not included
- 1 - LED Medium A19 8w Max. 120v - Not included
- 1 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

- 1 Body - Polycarbonate - White

Safety Listing:

- Safety Listed for Wet Locations

Instruction Sheets:

- English (HC-223)
- French (F-009)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Acrylic	Clear Beveled	4									

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	7 1/4	4 1/4			15 1/4	

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	8765-15	1	785652876554	8.78	8.18	16.38	0.681	2.9	150	Yes

NJ Pallet		80		48	40	72	80	232		No
NV Pallet		96		48	40	72	80	279		No