



# S9672

36W/LED/HID/2700K/100-277V E26  
36 watt - LED HID Replacement; 2700K; Medium base; 100-277 volts

## Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP65 rated
- For outdoor & indoor use
- Base up, base down or horizontal operation
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- cULus listed

## Additional Technical Specifications

- Power Factor >0.9
- Operating temperature range -20°C to 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V

Minimum lamp compartment dimensions:

235mm x 235mm x 440mm (9.25" x 9.25" x 17.3")

Optional accessory: In-line surge protector [80-929](#)



S9672

Item Number	Product Line	UPC	Input Voltage	Watts	Incandescent Equivalent	Fluorescent Equivalent	HID Equivalent
S9672	Hi-Pro	045923096723	100 - 277	36	200W	55W	150W

  

Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens

Medium	E26	36W/LED/HID/2700K/100-277V E26	Non-Dimmable	White	9-1/4"	3.69"	4390
Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type
50000	2700	Warm White	80+	300	-20C (-4F) to a maximum of +65C (+149F)	12	Box
RoHS Compliant			UL or ETL Listed			Warranty	
Yes			Yes			<a href="#">5 Year Limited</a>	



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051