



9 watt LED Directional Retrofit Downlight - Gimbale; 4";
3000K; 40' Beam spread; 120 volts; Dimmable



- Solid State LED lighting
- Directional Downlight Retrofit
- Gimballed
- Long life
- Dimmable

S9464

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Fixture Type	Base	Lamp Code		
S9464	045923094644	120	9	45W	Retrofit	Connector	9WLED/DIR/4/40'/30K/120V		
Dimmable/Non-Dimmable		Suggested Dimmers		MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color
Dimmable		Compatible dimmers for S9464		3-5/16"	6"	600	50000	3000	Warm White
CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant	UL or ETL Listed	UL Classification		
90	40	8	Box	ENERGY STAR	Yes	Yes	cULus Classified - Wet Location Rated		
Warranty									
5 Year Limited									



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051