



S9777

17T8/LED/48-840/DR
17 watt T8 LED; 4000K; Medium Bi Pin base; 50000 Average
rated hours; 2200 Lumens

Features

- Direct Replacement - for use on Instant Start and Rapid Start ballasts with no rewiring required*
- Ballast required
- Solid State LED lighting
- High efficacy
- Long life
- 5 year Limited warranty
- Dimmable*
- Compatible with emergency ballasts*
- All glass tube

*May not be compatible with all rapid start, dimmable, and emergency ballasts.

View:

[Ballast Compatibility Chart](#)

[Dimming Ballast Compatibility Chart](#)

[Emergency Ballast Compatibility Chart](#)

This item has been discontinued.
Possible replacement:

- [S9977](#)



S9777

Item Number	UPC	Watts	Fluorescent Equivalent	Lamp Shape	Base	ANSI Base	Lamp Code
S9777	045923097775	17	25W-32W	T8	Medium Bi-Pin	G13	17T8/LED/48-840/DR

Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI
White	48"	1.00"	2200	50000	4000	Cool White	82

Beam Spread Deg	Pack	Package Type	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty	Status
230	10	Box	Yes	Yes	cETLus - Damp Location Rated	5 Year Limited	Discontinued
Suggested Substitute							
S9977							



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051