

LED Flat Panel Fixture

2' x 2' - Dimmable



- 2x2 LED Flat Panel Fixture
- Easy Installation
- Instant-On
- Dimmable
- Suitable for Dry Locations Only
- Frosted Lens
- Mercury and UV Free
- Lasts up to 50,000 Hours
- UL Classified
- DLC Classified



Flat Panel

Order Number	L/FP2x2/43/DU/840/V101	L/FP2x2/44/DU/850/V101
Wattage	43W	44W
Lumens	3758.1 lm	4084 lm
CCT	4000K	5000K
CRI	>80	>80
Voltage	100-277V	100-277V
Dimmable	Yes	Yes
Power Factor	≥ .90	≥ .90
Operating Temp	-4° to 104° F	-4° to 104° F
Warranty	5 Years	5 Years

Note:

V. 1.5b