



3114503-782: Three Light Chandelier



Collection: Belton

UPC #:785652112836

Finish: Heirloom Bronze (782)

Dimensions:

Diameter:	19 7/8"	Overall Height:	52 1/4"
Height:	10 1/2"	Wire:	72" (color/Brown)
Weight:	6.75 lbs.	Mounting Proc.:	Center Lock-Up
		Connection:	Mounted To Box

Bulbs:

3 - Medium A19 60w Max. 120v - Not included

Features:

- Sloped ceiling mounting hardware included
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.
- Vintage lamp(s) recommended for aesthetics

Material List:

1 Body - Steel - Heirloom Bronze
1 6" Stem - Steel - Heirloom Bronze
3 12" Stem - Steel - Heirloom Bronze

Safety Listing:

Safety Listed for Dry Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (990CH311450_-BEL)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Clear Seeded	3	G560215-67			6 1/8	5 3/8				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	3/4			5		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Frt. Class	UPS Ship
Individual	3114503-782	1	785652112836	20	16.5	9.5	1.814	7.6	150	Yes
NJ Pallet		40		48	40	71	78.889	304		No
NV Pallet		40		48	40	72	80	472		No