



Item #:	UPC Code:
<b>K9787L-ORB</b>	<b>706411054433</b>
Product Family Name:	Finish:
	<b>Oil Rubbed Bronze</b>
Category:	Category Type:
<b>Light Kits</b>	<b>Light Kit</b>
Certification	
<b>4009339</b>	
Patents	
Notes:	



Image File Name:  
K9787L-ORB--  
1508876638.jpg



## MEASUREMENTS

Width:	Length:	Height:	Extension:
<b>5</b>	<b>5</b>	<b>1.5</b>	
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
<b>No</b>			<b>No</b>
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight
		<b>No</b>	<b>17.20</b>
Canopy Width:	Canopy Height:	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

## LAMPING

No. of Bulbs:	Light Type:			
<b>1</b>	<b>Led</b>			
Max Bulb Wattage:	Socket:			
<b>15</b>	<b>Led</b>			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
<b>Yes</b>		<b>30000</b>	<b>N</b>	<b>Yes</b>
LED Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
<b>Yes</b>	<b>3000</b>	<b>80</b>		<b>1300.000</b>



## SHIPPING

Carton Width:	Carton Height:	Carton Length:
<b>6.250</b>	<b>2.250</b>	<b>6.250</b>
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
<b>0.790</b>	<b>0.051</b>	<b>Yes</b>
Master Pack Width:	Master Pack Height:	Master Pack Length:
<b>6.750</b>	<b>12.250</b>	<b>32.380</b>
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
<b>21.340</b>		<b>25</b>

## SHADE / GLASS

Description:	Material:
Part No.:	Quantity:
Width:	Height:
	Length:

**LED**



Wet Location



ETL Intertek

LED

Yes

Yes

Yes