

### Features & Benefits

- Internal Driver
- Smooth, Consistent Light
- UL for Safety
- No UV, No Mercury
- Long Life
- High CRI
- Instant on, no delay or warm up time
- Convenient and quick installation
- Utilizes non-shunted(rapid start) sockets
- Compatible with controls and sensors
- Works in cold temperature applications
- 5 Year Warranty
- Made of Glass



Commercial Grade **LED T8 Lamp**



**Flex™**  
Internal Driver **LED T8 Lamp**

### Specification Data

Order Code	Model No.	Length	Lamp Wattage	Input Voltage	CCT	Initial Lumens	CRI	Beam Angle	LPW	Life	Operating Temp.	DLC
930-450	L48T8/835/14G-ID	48	14	120-277	3500	1800	83	325	120	50000	-20 ~ 40	Yes
907-037	L48T8/840/14G-ID	48	14	120-277	4000	1800	83	325	120	50000	-20 ~ 40	Yes
908-641	L48T8/850/14G-ID	48	14	120-277	5000	1800	83	325	120	50000	-20 ~ 40	Yes

### Ordering Information

EXAMPLE: **L48T8/840/14G-ID**

<b>L</b>	<b>48</b>	<b>T8</b>	<b>8</b>	<b>40</b>	<b>14 G</b>	<b>-</b>	<b>ID</b>
<b>Manufacturer's Code</b>	<b>Normal Length</b> 48=48"	<b>Lamp Shape</b> T8=T8	<b>CRI</b> 8=>80	<b>CCT</b> 50=5000K 40=4000K 35=3500K	<b>Wattage</b> 14G=14W		<b>Internal Driver</b>

### Wiring diagram

