

Molded Case Circuit Breakers

QJ 225A Frame

Type QJ2^②

Continuous Current Rating @ 40°C	2-Pole		3-Pole	
	240V AC		240V AC	
	Catalog Number	List Price \$	Catalog Number	List Price \$
60	QJ22B060■	422.00	QJ23B060	1106.00
70	QJ22B070■	422.00	QJ23B070	1106.00
80	QJ22B080■	422.00	QJ23B080■	1106.00
90	QJ22B090■	422.00	QJ23B090■	1106.00
100	QJ22B100	422.00	QJ23B100	1106.00
110	QJ22B110■	422.00	QJ23B110	1106.00
125	QJ22B125	422.00	QJ23B125	1106.00
150	QJ22B150	422.00	QJ23B150	1106.00
175	QJ22B175	422.00	QJ23B175	1106.00
200	QJ22B200	422.00	QJ23B200	1106.00
225	QJ22B225	422.00	QJ23B225	1106.00

Type QJH2^②

60	QJH22B060■	1010.00	QJH23B060■	1548.00
70	QJH22B070■	1010.00	QJH23B070■	1548.00
80	QJH22B080■	1010.00	QJH23B080■	1548.00
90	QJH22B090■	1010.00	QJH23B090■	1548.00
100	QJH22B100■	1010.00	QJH23B100	1548.00
110	QJH22B110■	1010.00	QJH23B110	1548.00
125	QJH22B125	1010.00	QJH23B125	1548.00
150	QJH22B150	1010.00	QJH23B150	1548.00
175	QJH22B175■	1010.00	QJH23B175	1548.00
200	QJH22B200	1010.00	QJH23B200	1548.00
225	QJH22B225	1010.00	QJH23B225	1548.00

Type QJ2H^②

60	QJ22B060H■	1255.00	QJ23B060H■	1964.00
70	QJ22B070H■	1255.00	QJ23B070H■	1964.00
80	QJ22B080H■	1255.00	QJ23B080H■	1964.00
90	QJ22B090H■	1255.00	QJ23B090H■	1964.00
100	QJ22B100H■	1255.00	QJ23B100H	1964.00
110	QJ22B110H■	1255.00	QJ23B110H■	1964.00
125	QJ22B125H	1255.00	QJ23B125H	1964.00
150	QJ22B150H	1255.00	QJ23B150H	1964.00
175	QJ22B175H■	1255.00	QJ23B175H	1964.00
200	QJ22B200H	1255.00	QJ23B200H	1964.00
225	QJ22B225H	1255.00	QJ23B225H	1964.00

Type HQJ2H^②

100	—	—	HQJ23B100H	▲2234.00
110	—	—	HQJ23B110H	▲2234.00
125	—	—	HQJ23B125H	▲2234.00
150	—	—	HQJ23B150H	2234.00
175	—	—	HQJ23B175H	▲2234.00
200	—	—	HQJ23B200H	2234.00
225	—	—	HQJ23B225H	▲2234.00

QJ2

Internal Accessories (Factory installed only) (3-pole only)^③

Add suffix to catalog number and adder to list price.

Control Voltage		Shunt Trip		Auxiliary Switches				Shunt Trip and 1A and 1B Auxiliary Switch	
AC	DC	Suffix	List Adder \$	Suffix	List Adder \$	Suffix	List Adder \$	Suffix	List Adder \$
120/240		00S01■	325.	A01■	265.	A02■	532.	01S01■	590.
	24	00S07■	325.	A01■	265.	A02■	532.	01S07■	590.
	125	00S11■	325.	A01■	265.	A02■	532.	01S11■	590.

■ Built to order. Allow 2-3 weeks for delivery.

▲ Built to order. Allow 6-8 weeks for delivery.

③ See **Note: A** page 6-73.

Note: QJ breakers are UL Listed for reverse feed applications.

② HACR rated.

③ Internal accessories are not available on 2-pole QJ breakers.

Selection/Dimensions

Ordering Information

Load side TA1Q300 lugs are mounted and included when circuit breaker is ordered. For line and load lugs (TA1Q300) installed at no additional charge, add suffix "L" to catalog number.

50°C Calibration - See page 6-84.

400HZ. - See page 6-84.

Shipping Weights

QJ2, QJH2, QJ2H, HQJ2H		
Number of Poles	Number per Carton	Shipping Weight (lbs.)
2	10	30
3	10	41

Lugs For 75°C Wire^①

Catalog Number	Lug Body	Lug Wire Range
TA1Q300	Al	(1) #6—300 kcmil Cu (1) #4—300 kcmil Al
TC1Q250	Cu	(1) #6—250 kcmil Cu

Enclosures (Neutral Included)

Type	Catalog Number	List Price \$
1	EB3225(S)(F)	226.00
3R (2-pole)	WB2225	418.00
3R (3-pole)	WB3225	459.00

UL 489 Interrupting Ratings

Breaker Type	AIR @ 240V AC
QJ2	10,000
QJH2	22,000
QJ2H	42,000
HQJ2H	100,000

