



### SF339ORB: 3 - Light Semi-Flush Mount

#### Dimensions:

<b>Diameter:</b>	20"	<b>Wire:</b>	8"
<b>Height:</b>	9 5/8"	<b>Mounting Proc.:</b>	Cap Nuts
<b>Weight:</b>	14.5 lbs.	<b>Connection:</b>	Mounted To Box

#### Bulbs:

3 - Medium A19 75w Max. 120v - Not included

#### Features:

•

#### Material List:

1 Body - Steel - Oil Rubbed Bronze

#### Safety Listing:

Safety Listed for Damp Locations

#### Instruction Sheets:

Trilingual (English, Spanish, and French) (SF339)



**Collection:** Lennon

**UPC #:**014817567410

**Finish:** Oil Rubbed Bronze (ORB)

#### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Linen	Ivory Linen	1				7	19 3/4				

#### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	3/4			14		

#### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	SF339ORB	1	014817567410	23.75	23.75	16	5.223	18.1	250	Yes

Feiss reserves the right to revise the design of components of any product due to parts availability or change in safety listing standards without assuming any obligation or liability to modify any products previously manufactured and without notice. This literature depicts a product design that is the sole and exclusive property of Feiss . In compliance with U.S copyright and patent requirements, notification is hereby presented in this form that this literature, or the product it depicts, is not to be copied, altered or used in any manner without the express written consent of, or contrary to the best interests of Feiss LLC ½ A Generation Brands Company.

NJ Pallet		15		48	40	75.75	84.167	271.5		No
NV Pallet		15		48	40	75.75	84.167	271.5		No