



Item #: F300-BN	UPC Code: 706411029936
Product Family Name: Retro	Finish: Brushed Nickel
Category: Interior Fan	Category Type: Table Fan
Certification 3148610	
Patents	
Notes:	



Alternate View



Image File Name:

F300-BN--
1377184320.jpg



MEASUREMENTS

Blade Finish:		Reversible Blades:	
		No	
Blade Material:		Slope:	
Aluminum		No	
Blade Sweep:	No. of Blades:	Blade Pitch:	Hanging Weight:
11	4	14	5.95
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:
		72	70x70x12mm

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	1253		1410		1525
Amps:	0.14		0.16		0.20
Watts:	15.700		19.000		23.500
CFM:	2750.00		3500.00		4750.00
CFM/Watts:	175.16		184.21		202.13



FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
No	No	No
	Included Remote Control:	Included Wall Control:
	Compatible Remote Control[s]:	Compatible Wall Control[s]:

LAMPING

No. of Bulbs:	Light Type:			
	N/A			
Max Bulb Wattage:	Socket:			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight
No	No			
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				

GLASS

Description:	Material:	
Part No.:	Quantity:	
Width:	Height:	Length:



SHIPPING

Carton Width:	Carton Height:	Carton Length:
8.900	12.610	12.000
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
7.700	0.779	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
18.250	13.500	25.750
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
33.000		1
		Master Pack:
		4



Title 17

Yes



ETL Intertek

Yes

For additional information, please contact Customer Care: 1-800-221-7977

Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties

Rev 12.31.2015