

4U Series 120V Xenon Collection
22" Xenon Harmonization 120V Cabinet Light -
WHT
4U120X22WHT (Textured White)



Dimensions

Height	1.25"
Length	22.00"
Width	4.50"

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____

Ordering Information

Product ID	4U120X22WHT
Finish	Textured White
Available Finishes	BZT, NIT, WHT
Collection	4U Series 120V Xenon Collection

Dimensions

Weight	2.00 LBS
--------	----------

Specifications

Material	Aluminum
Glass Description	Frosted

Electrical

Dimmable	Yes
Voltage	108-132V
Input Voltage	Single(120)
Operating Voltage Range	108-132V
Switch Type	Hi-Low-Off, Rocker

Qualifications

Safety Rated	Dry
Expected Life Span	2500 Hours
Warranty	www.kichler.com/warranty

Installation

Wire Connectors	Wire Nuts
Direct Wire	Yes
Knockouts	0.5 in
Number of Knockouts	7
Modular	Yes

Primary Lamping

Light Source	Incandescent
Lamp Included	Included
Number of Lights/LEDs	3
Max or Nominal Watt	20W
Socket Type	Bi-Pin
Lamp Type	G8
Bulb Product ID	12090CLR
Dimming	Yes