

# 4U Series 120V Xenon Collection

## 30" Xenon Harmonization 120V Cabinet Light - WHT

4U120X30WHT (Textured White)



### Dimensions

Height	1.25"
Length	30.00"
Width	4.50"

Project Name: \_\_\_\_\_  
Location: \_\_\_\_\_  
Type: \_\_\_\_\_  
Qty: \_\_\_\_\_  
Comments: \_\_\_\_\_

### Ordering Information

Product ID	4U120X30WHT
Finish	Textured White
Available Finishes	BZT, NIT, WHT
Collection	4U Series 120V Xenon Collection

### Dimensions

Weight	2.70 LBS
--------	----------

### Specifications

Material	Aluminum
Diffuser Description	Frosted

### Electrical

Dimmable	Yes
Voltage	108-132V
Input Voltage	Single(120)
Operating Voltage Range	108-132V
Switch Type	Hi-Low-Off, Rocker

### Qualifications

Safety Rated	Dry
Expected Life Span	2500 Hours
Warranty	<a href="http://www.kichler.com/warranty">www.kichler.com/warranty</a>

### Installation

Wire Connectors	Wire Nuts
Direct Wire	Yes
Knockouts	0.5 in
Number of Knockouts	7
Modular	Yes

### Primary Lamping

Light Source	Incandescent
Lamp Included	Included
# of Bulbs/LED Modules	4
Max or Nominal Watt	20W
Socket Type	Bi-Pin
Lamp Type	G8
Bulb Product ID	12090CLR
Dimming	Yes

#### Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.