

112-05019

HellermannTyton

Article Number: 112-05019



Description: Standard Cable Tie, 8" Long, UL Rated, 50lb Tensile Strength, PA66, Natural, 100/pkg

Base Data		
	Local Order Number	T50R9C2
	Type	T50R
	Color	Natural (NA)
	Features and benefits	• Engineered and manufactured for maximum performance and quality. • Made from 100% high-quality plastic to ensure efficient recycling. • Inside serration for a strong hold onto bundles. • Easy application either manually or with a processing tool. • Bent tail allows for simpler insertion.
	Quantity Per	bag
	Product Description	T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
	Global Part Name	T50R-PA66-NA
	Short Description	Standard Cable Tie, 8" Long, UL Rated, 50lb Tensile Strength, PA66, Natural, 100/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	50.0lbs
	Minimum Tensile Strength (Metric)	225.0N
	Length L (Imperial)	8.0"
	Length L (Metric)	202.0mm
	Fixation Method	None
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	0.18"
	Width W (Metric)	4.6mm
	Bundle Diameter Min. (Imperial)	0.06"

112-05019



Product Dimensions	Bundle Diameter Min. (Metric)	1.5mm
	Bundle Diameter Max. (Imperial)	1.97"
	Bundle Diameter Max. (Metric)	50.0mm
	Thickness T (Imperial)	0.05"
	Thickness T (Metric)	1.2mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	US MILSPEC	SAE-AS81531
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
	Certification/Specification WEB	BACS38K, CAGE Code 53421, VG 95387 Teil 4 Ausgabe: 2008-12
	UL Listed (US and Canada)	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	1.3kg