

ASHLAND BAY COLLECTION

Ashland™ Bay 3 Light Vanity Light Polished Nickel™
45772PN (Nickel)



Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____

Certifications/Qualifications

Location Rating	Damp
-----------------	------

Dimensions

Base Backplate	9.00 X 5.00 OVAL
Chain/Stem Length	0.00"
Weight	5.30 LBS
Extension	6.50"
Height from center of Wall opening (Spec Sheet)	2.50"
Height	8.00"
Width	24.00"

Mounting/Installation

Interior/Exterior	Interior
Mounting Style	Wall Mount
Mounting Weight	3.50 LBS

Primary Lamping

Lamp Included	Not Included
Lamp Type	A19
Light Source	Incandescent
Max or Nominal Watt	100W
# of Bulbs/LED Modules	3
Socket Type	Medium

Product/Ordering Information

Finish	Nickel
UPC	783927482912.00

Specifications

Diffuser Description	Clear Seeded Ribbed
----------------------	---------------------

Kichler
7711 East Pleasant Valley Road Cleveland, Ohio 44131-8010 Toll
free: 866.558.5706 or kichler.com

Notes:
1) Information provided is subject to change without notice.
All values are design or typical values when measured under
laboratory conditions.
2) Incandescent Equivalent: The incandescent equivalent as
presented is an approximate number and is for reference only.



