

- PDF was successfully created - CLICK LINK TO DOWNLOAD =>[http://www.satco.com/media/PDF/satco\\_product\\_6855.pdf](http://www.satco.com/media/PDF/satco_product_6855.pdf)



# S9841

9.5A19/OMNI/220/LED/35K/GU24

9.5 watt; A19 LED; 3500K; GU24 base; 220° beam spread; 120 volts

## Features

- Solid State LED lighting
- A shaped replacement lamp
- Long life
- Dimmable



S9841

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9841	045923098413	120	9	60W	0.88	A19	GU24

Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
9.5A19/OMNI/220/LED/35K/GU24	Dimmable	<a href="#">Compatible dimmers for S9841</a>	Frosted	4-3/16"	2-3/8"	800	25000

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
3500	Neutral White	80	220	-20C (-4F) to a maximum of +45C (+113F)	24	Box	ENERGY STAR
RoHS Compliant	Fixture Type	UL or ETL Listed	UL Classification	Warranty			
Yes	Enclosed Rated	Yes	cULus - Damp Location Rated	<a href="#">3 Year Limited</a>			



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051