Technical Data Sheet



Catalog No. K1XGF12-1

Characteristics	
Phase	1
KVA	1
Primary	120X240V
Secondary	12/24V
Conductor	Copper
Temp. Rise	115° C
Frequency	60 HZ
Taps	None
ESS	No
Insulation	180° C
Weathershield	N/A
Wall Bracket	Built-In
Weight(lbs)	28
Sound(dB)	40

All units are UL listed and are designed in accordance with applicable NEMA, ANSI and IEEE standards. Transformers are dry-type AA, non-ventilated NEMA 3R enclosure. Transformers are wall mounted. Wall mounting bracket is built into the enclosure. Paint color is ANSI 61.





