



Representative Image

Catalog No. AQU1424RCXAXT1B4
Description: PRO-STK 240V 1PH 400A FT 42CR CU

UPC No 783175120208

Home > Panelboards > A-Series > Pro-Stock Lighting Panel

Maximum system voltage is upto 240Vac for AQ panelboard line -Field installable kits allow you to shift gears on the fly-Standard Pro-Stock panels have the capability of adding sub-feed breakers or feed-thru lugs in the field -All panel are convertible AQU1424R 76.0 in

Descriptors

Category	Pro-Stock Lighting Panel
GO Schedule	32

Specifications

Voltage	240 V
Phase	1
Panel Rating	400
No of Circuits	42
Feed Thru	Yes
Bus	Copper
Interior Type	AQU
Box/Front Height	76.0 in
Interior Description	Pro-Stock 240V, 1PH, 400A 42Cir. CU
GSA Compliance	No

Publications

Title	Publication No.	Publication Type
1 Phase 42 Circuit Interior		
Pro-Stock* 1 Phase 42 Circuit Interior	3000115258PV4	Drawings-Outline and Dimensional

Additional Documentation: Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.