

A19LED101

4.5W LED Filament

DESCRIPTION

Perfect for lanterns or any exposed bulb application
Classic filament design creates a unique vintage feel in any room
15,000 hours lifespan is guaranteed.
EMC Compliant

PERFORMANCE

- Compatible with most dimmers;
- Dimming smoothly from 10% to 100%.
- 40W Incandescent replacement;
- UL compliant, FCC certified

CONSTRUCTION

- Glass cover
- Filament
- Integrated driver
- Aluminium E26base

INSTALLATION

- Directly replace a 40W incandescent lamp.
- Suitable for damp locations;
- 120V AC input

PHOTOMETRIC

Model# A19LED101

Luminous flux	400LM
Input wattage	4.5W
Lumens per watt	88.8LM/W
Beam angle	300°

Elitco Lighting



LED Filament

A19LED101



Specifications

Model #	A19LED101
Input voltage	120V AC
Color Temperature	2200K
CRI	>80
Current	44mA
Watts	4.5W
Watt Equivalent	40W
Lumens	88.8LM/W
Beam angle	300°
Dimmable	Yes
Lens	N/A
Rating	FCC
Dimensions	2.36*3.94"
Power Factor	0.8
Mounting	Connect to city power directly
LED type	EPISTAR
Average Life (Hrs)	15,000 hrs.
Warranty	2 Years Limited