



# S9379

18.5W/LED/9"FLUSH/30K/RD/BN  
18.5 watt; 9" Flush Mount LED Fixture; 3000K; Round Shape;  
Brushed Nickel Finish; 120 volts

## Features

- Surface mount fixture
- Solid State LED lighting
- Long life
- 5 Year limited warranty
- Dimmable
- Damp location rated



S9379

Item Number	Product Line	UPC	Voltage	Watts	Incandescent Equivalent	Fixture Type	Base
S9379	BLINK	045923093791	120	18.5	100W	Flush Mount	Connector

Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
18.5W/LED/9"FLUSH/30K/RD/BN	Dimmable	<a href="#">Compatible dimmers for S9379</a>	Brushed Nickel	1"	9.00"	1200	40000

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
3000	Warm White	80+	108	-18C (0F) to a maximum of +46C (+115F)	12	Box	ENERGY STAR
Material		RoHS Compliant	UL or ETL Listed	UL Classification	Warranty		
Housing: Die cast aluminum		Yes	Yes	cETLus - Damp Location Rated	<a href="#">5 Year Limited</a>		



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051