



Representative

Catalog Number: ASC 3/0 TN
Product ID: 7TAA262050R0126
UPC Number: 78378669593
Status: Active

Tin-Plated Aluminum Straight Splices, 3/0 Stranded AL9CU UL listed, installing dies TV, 66, 167, 467, 10A. Length 2-5/8 inch x 49/64 inch Diameter. Oil Stop. Oxide Inhibitor. Ruby Caps.

- Made of Aluminum for High Strength and High Conductivity.
- Solid Center Stop Ensures Proper Cable Insertion.
- Dual-Rated for Use with Aluminum and Copper Conductors.
- Prefilled with Oxide Inhibitor to Prevent Oxidation and Keep Out Moisture.
- All Splices Marked with Conductor Sizes and Die References for Easy Identification.
- Meets or Exceeds ANSI C119.4 Specifications. Splices with Tin-Plating are UL Listed through 1000 kcmil.

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Straight Compression Splice
Special Features	Dual Rated for Aluminum or Copper Conductors. Prefilled with Oxide Inhibiting Compound. Solid Center Stop ensures proper Cable insertion.
Application	Cable Splice
Standard	ANSI C119.4
Size	2-5/8 inch
Connection	Compression
Conductor Range	Concentric 3/0
Number Of Conductors	2
Material	Aluminum
Finish	Tin-Plated
Insulation	None

Packaging

Inner Quantity	50
Outer Quantity	250
Outer Dimensions (inches)	17.75x14x8.5
Weight Uom	8.5 lbs. per 100

Documents / Support Tools

Safety Data Sheet (SDS) Global	SDS-00041-TB2
--------------------------------	---------------

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com