



8592-02: One Light Outdoor Wall Lantern



Collection: New Castle

Simple Details Create Stylish Outdoor Wall Lantern. Polished Solid Brass and Clear Glass.

Simple details create a stylish outdoor wall lantern. Polished Brass and clear glass.

UPC #:785652859229

Finish: Polished Brass (02)

Dimensions:

Width:	4 1/4"	Extends:	5 1/2"
Height:	8 1/4"	Wire:	6 1/2" (color/Black/White)
Weight:	1.4 lbs.	Mounting Proc.:	Cap Nuts
		Connection:	Mounted To Box
		Bulb Appearance:	Clear

Bulbs:

1 - Medium A19 100w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

- 1 Body - Brass - Polished Brass
- 1 Canopy - Brass - Polished Brass

Safety Listing:

Safety Listed for Wet Locations
Safety Listed for Wet Locations

Instruction Sheets:

English (HC-231)
French (F-009)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear	4	G500052-32		3 3/8	4 5/16					

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate			2 1/16	4 1/2	2 3/4	5 1/2

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	8592-02	1	785652859229	6.75	5.75	9	0.202	1.75	100	Yes
Master Pack		6	10785652859226	18	14.5	9.75	1.473	11.7	100	Yes
NJ Pallet		252		48	40	72	80	452.76		No
NV Pallet		216		48	40	68	75.556	422		No