



# SPECIFICATION SHEET

## T28 High Lumen LED Lamp

Item Number **05166**

### Specifications

Energy Used (Watts).....	54
Incandescent Equivalent Wattage .....	400
CFL Equivalent Wattage .....	105
HID Equivalent Wattage.....	250
Domestic Code .....	54T28/LED/HL/E39/50
Volts .....	120-277
Brightness (Lumens) .....	6480
Average Rated Hours.....	40,000
Light Appearance (Kelvin).....	5000
Beam Spread .....	360°
CRI .....	80
Efficacy (LPW).....	120
Number of LED Modules.....	180
Package Type .....	Box
Can be used in totally enclosed fixtures.	
IP65 Rating - Protection against dust and water jets	
Built-in surge protection - Able to withstand momentary voltage surges up to 6000V	



### Physical Characteristics

Color Designation .....	Daylight
Housing Material.....	Aluminum
Base.....	Mogul (E39)
MOL .....	10.55"



### Limited Warranty

This lamp is warranted to be free from defects in material and workmanship for 5 years (based on using 12 hours per day).

### Warning

- Turn power off before inspection, installation, or removal.
- Risk of electric shock - Do not use where exposed to water or weather.
- Suitable for Damp Locations - The lamp is suitable for use in wet locations when used in an outdoor rated fixture.
- Do not open - no user serviceable parts inside.
- This device is not intended for use with emergency exit luminaires or emergency exit lights.
- This device complies with Part 15 of the FCC rules and has been tested and found to comply with the limits for a Class B digital device. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. Any changes or modifications not expressly approved by the manufacturer could void the user's authority to operate the equipment.

*Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.*

**Call 1-800-999-2226 or visit [www.westinghouselighting.com](http://www.westinghouselighting.com).**

©, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.

Used under license by Westinghouse Lighting. All Rights Reserved.