

ESTELLA COLLECTION

Estella™ 2 Light LED Wall Light Textured Architectural Bronze

49608AZTLED (Bronze)



Project Name: _____

Location: _____

Type: _____

Qty: _____

Comments: _____

Certifications/Qualifications

Location Rating	Wet
Title 24 Compliant	Yes

Dimensions

Base Backplate	4.50 X 5.75
Chain/Stem Length	0.00"
Weight	3.26 LBS
Extension	4.25"
Height from center of Wall opening (Spec Sheet)	8.25"
Height	16.50"
Width	6.00"

Electrical

Input Voltage	Single(120)V
---------------	--------------

Mounting/Installation

Interior/Exterior	Exterior
Mounting Style	Wall Mount
Mounting Weight	3.39 LBS

Photometrics

Color Rendering Index	90.00
Color Temperature Range	3000.00
Delivered Lumens	880.00
Delivered Efficacy (Lumens/Watt)	99.00
Kelvin Temperature	3000.00

Primary Lamping

Dimmable	Yes
Equivalent Light Source	Incandescent
Expected Life Span	35000.00
Lamp Included	Integrated
Light Source	LED
Max or Nominal Watt	8W
# of Bulbs/LED Modules	2

Product/Ordering Information

Finish	Bronze
UPC	783927458757.00

Specifications

Diffuser Description	Clear Tempered Glass With Inside Etch
----------------------	---------------------------------------

Kichler
7711 East Pleasant Valley Road Cleveland, Ohio 44131-8010
Toll free: 866.558.5706 or kichler.com

Notes:
1) Information provided is subject to change without notice.
All values are design or typical values when measured under laboratory conditions.
2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.



