

# A-Shape LED

## LA19/9/840/ECO/D

### 9 Watt LED A19

- Dimmable down to 10%\*
- 85% energy savings compared to 60W incandescent



|                           |                     |
|---------------------------|---------------------|
| <b>Item #</b>             | LA19/9/840/ECO/D-78 |
| <b>Product Code</b>       | 78014               |
| <b>UPC</b>                | 751338000476        |
| <b>Watts</b>              | 9                   |
| <b>Volts</b>              | 120                 |
| <b>Lamp Shape</b>         | A19                 |
| <b>Base</b>               | E26 Medium          |
| <b>CRI</b>                | 80                  |
| <b>Color Temp</b>         | 4000K               |
| <b>Initial Lumens</b>     | 725                 |
| <b>Beam Spread</b>        | 240°                |
| <b>Average Rated Life</b> | 15,000              |
| <b>Temp Range</b>         | -20°C to 40°C       |
| <b>MOL</b>                | 4.4"                |
| <b>Equivalent Wattage</b> | 60                  |
| <b>Warranty</b>           | 3 years             |

Specifications are subject to change without prior notice.

\*Compatible with most leading edge or incandescent style dimmers.

Not Rated for use in totally enclosed fixtures.

