



Representative

Catalog Number: 12005Y-200
Product ID: 7TAA234010R0007
UPC Number: 03448123180
Status: Active

ENT Flexible Raceway, Size 1/2 Inch, Nominal Inner Diameter 0.56 Inches, Nominal Outer Diameter 0.84 Inches, Minimum Bend Radius 6 Inches, Color Yellow, Length 200 Feet

- One piece ENT coupling, threaded terminator and rigid non-metallic conduit fittings are rated concrete tight without tape.
- Lightweight, hand bendable, and free from sharp edges which reduces installation time and saves money.

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Carlon
Type	ENT Flexible Raceway
Special Features	Recognized for use with PVC rigid non-metallic conduit fittings with all size of ENT.
Application	Flex-Plus Blue ENT is a non-metallic flexible raceway for use in walls, floors, and non-plenum ceilings.
Standard	UL E73317
Trade Size	1/2 Inch
Outside Diameter	0.84 Inches
Inside Diameter	0.56 Inches
Length	200 Feet
Material	Non-Metallic
Color	Blue

European Specifications (ETIM)

ETIM	EC001175 Corrugated plastic hose
Nominal diameter	12.7mm
Nominal size in inch	1/2 inch
Outer diameter	21.336mm
Inner diameter	14.224mm
Material	PVC
Colour	Other
Sheathing material	Not sheathed
Approved according to DIN EN 61386-23	N
Approved according to UR	N
Approved according to LUL/British Standard	N
Approved according to Lloyd's Register TA	N
Approved according to UTAC	N
Approved according to DIN 5510	N
Approved according to NF F 16-101	N

Packaging

Outer Quantity	200
Outer Dimensions (inches)	1x1x1
Weight Uom	2.13 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com