

MP260GFA | US2:MP260GFA

Class A GFCI (Gen 1) - 2 Poles, 60A, 10kA IR	
List Price	Show prices
Customer Price	Show prices
DataSheet in PDF	Download
Service & Support (Manuals, Certificates, FAQs...)	Download

Image similar

Product		
Article Number (Market Facing Number)	MP260GFA US2:MP260GFA	
Product Description	Class A GFCI (Gen 1) - 2 Poles, 60A, 10kA IR	
Product family	Ordering Data Overview	
Product Lifecycle (PLM)	PM300:Active Product	
Price data		
Price Group	NR0	
List Price	Show prices	
Customer Price	Show prices	
Metal Factor	None	
Delivery information		
Export Control Regulations	AL : N / ECCN : EAR99	
Standard lead time ex-works	1 Day/Days	
Net Weight (lb)	0.992 lb	
Product Dimensions (W x L x H)	Not available	
Packaging Dimension	1.969 x 6.693 x 2.756	
Package size unit of measure	in	
Quantity Unit	1 Piece	
Packaging Quantity	1	
Additional Product Information		
EAN	Not available	
UPC	887621216030	
Commodity Code	8536200020	
LKZ_FDB/ CatalogID	LV10.1	
Product Group	5200	
Country of origin	Philippines	
RoHS Compliance	not available	
Returnable	Yes	
Obligation Category for taking back electrical and electronic equipment after use	No obligation to take back electrical and electronic equipment after use	
Classifications		
	Version	Classification
eClass	5.1	27-37-92-01
eClass	6	27-37-92-01
eClass	7.1	27-37-92-01
eClass	8	27-37-92-01
eClass	9	27-37-92-01
eClass	9.1	27-37-92-01
ETIM	5	EC002498
ETIM	6	EC002498
UNSPSC	15	39-12-16-01