



Product Listing > Product Detail > Lamps > HID > Metal Halide > Standard Protected > MP400/BU 108294 400W MP ED37 EX39 BU PROLUME > Lamps > HID > Metal Halide > Pulse Start > MH350/BU/PS 108291 350W MH ED37
MOG BU PS PROLUME ***UN2911***



MH350/BU/PS 108291
350W MH ED37 MOG BU
PS PROLUME
*****UN2911*****

Product Number: 108291


UPC: 807154182916

[Log In for Price and Availability](#)

ANSI Code 1	M131/E
Applications	Roadway, Parking lot, retail, security, street, wall wash
Average Life (Hrs)	20000
Base	Mogul
Brand	ProLume
Bulb	ED37
CRI	65
Color Temperature	4000
Cross Reference - Osram Sylvania	MP350/400/PS/BU-ONLY/BT28
Design Lumens	29000
Dimensional Dwg	
Dimmable	Yes
HTS code	8539320040
Initial Lumens	37000
Inner Carton Quantity	1
Input Frequency (Hz)	60
KR85 Content	<120
Lens	Clear
Markets	Residential, Commercial
Master Carton Quantity	6
Maximum Overall Diameter	4.62
Maximum Overall Length	11.5
Nominal Length	11.5
Operating Position	Base Up
Prod Code	MH350/BU/PS
Product Category	Metal Halide
Product Description	350W MH ED37 MOG BU PS PROLUME ***U
Product Number	108291
Start Type	Pulse Start
UN2911	Yes
Wattage (W)	350



Lamps



Ballasts



Luminaires



Catalogs

Sell Sheets

New Products

Corporate Office:

Halco Lighting Technologies

2940 Pacific Drive

Norcross, GA 30071

Toll Free: 800.677.3334

Office: 770.242.3612

Fax: 800.880.0822

Email: customer care@halcolighting.com

