

Siemens Low Voltage Molded Case Circuit Breakers General Purpose MCCBs are Circuit Protection Molded Case Circuit Breakers. 3-Pole Common-Trip circuit breaker type BQ. Rated 240V (040A) (AIR 10 kA). Special features: Load side lugs are included.



Number of poles	3
Suitability for operation	Electrical Distribution
Electricity	
Continuous current rated value	40 A
Model	
product brandname	SIEMENS
Type of electrical connection	BOLT-ON
Mechanical Design	
Depth [in]	12.7 in
Design of the product	BQ
Height [in]	3.7 in
Width [in]	4.7 in
General product approval	
Standard	UL 489
last modified:	08/20/2017