



# S9802

15A21/LED/2700K/120V/4PK  
15 watt; A21 LED; 2700K; Medium base; 240' beam spread;  
120 volts; 4-pack

## Features

- A-Shaped replacement lamp
- 100w equivalent
- Approved for enclosed fixtures
- Damp location rated



**4** Pack

S9802

Item Number	UPC	Input Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9802	045923098024	120	15	100W	0.90	A21	Medium

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E26	15A21/LED/2700K/120V/4PK	Non-Dimmable	Frost	5-1/4"	2-3/8"	1500	15000

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	RoHS Compliant
2700	Warm White	80	240	-20C (-4F) to a maximum of +45C (+113F)	4	4Pk	Yes

Fixture Type	UL or ETL Listed	UL Classification	Warranty
Enclosed Rated	Yes	cULus - Damp Location Rated	<a href="#">3 Year Limited</a>



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

