



GE
Lighting

35535 - GE LED MR16

LED5.5DMR1683035

- ☞ The Value 12 Volt AC/DC MR16 is an Energy-efficient LED lamps.
- ☞ Long life
- ☞ Energy Star Rated
- ☞ Flood 35° beam
- ☞ White

Product Photo



GENERAL CHARACTERISTICS

Base Description	GU5.3
Base Type	Plug-in
Dimmable	Yes
Lamp Type	LED-MR
Primary Application	Track & Recessed
Product Color	White
Product Technology	LED
Rated Life (Hours)	25000 h
Dimmable / Non-Dimmable	Yes
10 Digit U	4316835535
Lamp Count	1
Life in Years	22.8 yr
Replacement Watts	35 W
Requested Structure	Carton
Estimated Energy Cost per Year	0.66
Base	E26
Bulb Shape	MR16

PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	1000 cd
Initial Lumens-nominal	420 lm
Color Rendering Index-CRI	80
Color Temperature	3000 K

PRODUCT INFORMATION

Product Code	35535
Description	LED5.5DMR1683035
Alternative Unit Of Measure	CASE
Standard Package Quantity	6
Ean UPC	043168355353
Standard Package GTIN	10043168355350
No Of Items Per Sales Unit	
No Of Items Per Standard Package	6
Sales Unit	Case
UCC	043168355353
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168355353
Standard Package GTIN	00043168355353
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168355353

DIMENSIONS

Bulb Max Overall Length-MOL	1.88 in
-----------------------------	---------

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	12 V
Input Voltage [nom]	12 V
Rated power (Watts)	5.5 W

CAUTIONS & WARNINGS

Caution

Risk of electric shock

Do not use where directly exposed to water

Not for use in totally enclosed luminaires

For use only with approved Class 2 transformers/drivers