# CHROMAPATH® BUILDER 45°

#### INCLUDES


# End-to-end connector plugs & mounting clips

#### COMPATIBILITY

FLUID VIEW® BLAZE™ ULTRA BLAZE™ DOUBLE BLAZE™ VALENT® VALENT® HD

VALENT® X AVENUE 24™ DAZZLE® RGB(W)

\_\_0.67 in



#### CHANNEL OPTIONS

SKU ALUMINUM	SKU WHITE FINISH	SKU BLACK FINISH	LENGTH	BUNDLE OPTION	INCLUDES PER CHANNEL
DI-CPCHA-4548	DI-CPCHA-4548W	DI-CPCHA-4548B	48 in.	Single	• 4x end-to-end connectors
DI-CPCHA-4548-10	DI-CPCHA-4548W-10	DI-CPCHA-4548B-10	48 in.	Pack of 10	<ul><li>2x mounting clips</li></ul>
DI-CPCHA-4596	DI-CPCHA-4596W	DI-CPCHA-4596B	96 in.	Single	•8x end-to-end connectors
DI-CPCHA-4596-10	DI-CPCHA-4596W-10	DI-CPCHA-4596B-10	96 in.	Pack of 10	<ul> <li>4x mounting clips</li> </ul>

#### PREMIUM DIFFUSION COVER AND END-CAP

## PRODUCT INFORMATION



#### PREMIUM DIFFUSION COVER (PD):

The ultimate in total diffusion for uninterrupted continuous LED light output. Note: warm shift in Kelvin of 75K and an

average 24% decrease in delivered lumens. Refer to install guide for optimal performance guidelines.

SKU	FORM FACTOR	LENGTH	BUNDLES
DI-CPCHC-PD48	PD Cover	48 in.	Single
DI-CPCHC-PD48-10	PD Cover	48 in.	Pack of 10
DI-CPCHC-PD96	PD Cover	96 in.	Single
DI-CPCHC-PD96-10	PD Cover	96 in.	Pack of 10
PRODUCT IMAGE	FOR	M FACTOR	
	45° Premium Diffusion End-Cap 5 extra sets		
SKU ALUMINUM	SKU WHITE FINIS	SH SKU I	BLACK FINISH
DI-CPEC-45PD	DI-CPEC-45PDW	DI-CP	EC-45PDB

#### STANDARD COVERS FROSTED / CLEAR AND END-CAPS

## PRODUCT INFORMATION

#### FROSTED COVER:

Protects LED tape light and slightly softens light. Note: Average warm shift in Kelvin of 35K and average 28% decrease in delivered lumens.



#### **CLEAR COVER:**

Protects the LED tape light with no visible color shift or change in delivered lumens.

SKU	FORM FACTOR	LENGTH	BUNDLES
DI-CPCHC-FR48	Frosted Cover	48 in.	Single
DI-CPCHC-FR48-10	Frosted Cover	48 in.	Pack of 10
DI-CPCHC-FR96	Frosted Cover	96 in.	Single
DI-CPCHC-FR96-10	Frosted Cover	96 in.	Pack of 10
DI-CPCHC-CL48	Clear Cover	48 in.	Single
DI-CPCHC-CL48-10	Clear Cover	48 in.	Pack of 10
DI-CPCHC-CL96	Clear Cover	96 in.	Single
DI-CPCHC-CL96-10	Clear Cover	96 in.	Pack of 10

#### PRODUCT IMAGE FORM FACTOR



45° Standard End-Cap 5 extra sets

SKU ALUMINUM	SKU WHITE FINISH	SKU BLACK FINISH
DI-CPEC-45	DI-CPEC-45W	DI-CPEC-45B

## **MOUNTING OPTIONS**

MOUNTING CLIPS



SKU DESCRIPTION DI-CPMC2-SCR4 Pack of 2 Clips / 4 screws DI-1630-20 Pack of 20 Clips / 40 screws

VERTICAL MOUNTING **BRACKETS** 

DESCRIPTION SKU

DI-1912 Pack of 2

END-TO-END CONNECTOR **PLUGS** 

SKU DESCRIPTION

DI-1631-10 Pack of 10

ROTATING **CLIPS** 

MOUNTING



Includes: Pair of clips with screws

ALUMINUM WHITE

BLACK

DI-CPCH-RC-BA DI-CPCH-RC-WH DI-CPCH-RC-BL