



S9497

6.5MR16/LED/40°/35K/12V
6.5 watt; LED MR16 LED; 3500K; 40° beam spread; GU5.3
base; 12 volt AC/DC

Features

- Silver back MR16 reflector
- Direct replacement for 50watt Halogen lamps
- Approved for enclosed fixtures
- Dimmable



S9497

Item Number	UPC	Voltage	Watts	Power Factor	Lamp Shape	Base	ANSI Base
S9497	045923094972	12v AC/DC	6.5	0.96	MR16	GU5.3	GU5.3

Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
6.5MR16/LED/40°/35K/12V	Dimmable	Compatible dimmers for S9497	White	1 3/4"	2"	500	25000

Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	ENERGY STAR	RoHS Compliant	UL or ETL Listed
3500	Neutral White	80	40	12/48	ENERGY STAR	Yes	Yes
Warranty							
3 Year Limited							



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

